Hei-VAP Expert Control



Adds numerous smart features to the Hei-VAP Expert, as well as an overview of all parameters and the current process

- 5" touch display for controlling the entire system including the vacuum and the cooling temperature
- For precise monitoring, the pictogram on the display also symbolizes active functions
- Separate knobs for quick access: the right one for direct vacuum control, the left one for the rotation
- Setting of values either via the touch display or the separate quick access knobs
- Direct access to two favorites on the start screen
- Expandable solvent library. You can also transfer your own favorites to other devices using a USB stick
- Define and save own evaporation processes (ramps)
- Automatically evaporate with the Dynamic AUTO_{accurate} Program (DAA). Convenient and customizable: from foam avoidance to highly efficient evaporation
- With USB and Micro SD interface for easy installation of software updates and transfer of individual favorites from one device to another



Hei-VAP Expert - Technical Data

Rotation speed indicator	5" LCD color graphic display
Permissible ambient conditions	5 – 31 °C at 80 % rel. humidity 32 – 40 °C decreasing lineary up to max 50% rel. humidity
Protection class DIN EN 60529	IP 20
Lift	Hand lift or Motor lift
Height adjustment speed	Hand lift models: manual Motor lift models: 25 mm/s
Height adjustment	155 mm
Drive	brushless DC motor with electronic speed control
Heating capacity	1,300 W
Temp. range heating bath	20 – 210 °C
Temperature accuracy bath	±1K
Overheat protection bath	cut-off at 5 °C over set temperature via separate PT 1000
Bath temperature setting	5" LCD color graphic display
Heating bath temperature control	electronic / digital
Secondary overtemp. cut off	250 °C
Material heating bath	stainless steel V4A
Diameter heating bath	255 mm
Volume heating bath	4.5
Display vapor temperature	Yes
Required accessories for display vapor temperature	Vapor temperature sensor
Integrated vacuum controller	Yes
Timer	Yes
Programmable ramps	Yes
Supply Power	1,400 W



Weight without glassware assembly	15 kg
Dimensions with glassware set G3 (w/d/h)	HL: 739 x 532 x 887 mm ML: 739 x 477 x 887 mm
Dimensions with glassware set G3 XL (w/d/h)	HL: 739 x 532 x 920 mm ML: 739 x 477 x 920 mm
Condensing surface	1,400 cm ²
Condensing surface XL condenser	2,200 cm ²
Max. size evaporating flask	5
Rotation speed range	10 - 280 rpm
Integrated Hei-CHILL controller	Yes
Vacuum program Dynamic AUTOaccurate requires AUTOaccurate sensor	Yes
Solvent libary	Yes



WWW.HOSKIN.CA

• ENVIRONMENTAL • INSTRUMENTATION • MATERIALS TESTING

• INTEGRATED SYSTEMS • RENTALS • SERVICE

Vancouver | Oakville | Montréal | Edmonton